

SATELLITE 4090XDVD Product Specifications

MODEL	PART NUMBER	DESCRIPTION	
4090XDVD	PAS409U-T2DW8	Intel® Celeron® 400MHz, 14.1" TFT , 64MB, 6.4bb HDD , Modem, DVD-ROM Windows 98 w/ dual linked Win95/98 Configuration Builder CD	
4090XDVD-NT	PAS409U-T2DN4	Intel® Celeron® 400MHz, 14.1" TFT , 64MB, 6.4bb HDD , Modem, DVD-ROM Windows NT Configuration Builder CD (CB Pro Compatible)	
PROCESSOR		Intel Celeron® 400Mhz (1.6v)	
Integrated Coprocessor		Yes	
Processor Cache (L1) Capacity		32KB: (16KB code; 16KB data)	
LEVEL 2 (L2) CACHE		Yes: 128KB Integrated into CPU (On-die)	
Data/Address Bus Width		64bit/32bit	
Local Bus Clock Speed		66 MHz	
SYSTEM ARCHITECTURE		<u>Chipset</u>	<u>Connecting Devices</u>
PCI BUS (v.2.1): (32-bit, 33 MHz)		Intel 440DX	Graphics Controller, Sound , Modem
ISA BUS: 16-bit, 8.33MHz		N/A	BIOS, KBC
MEMORY: 64Mbit SDRAM, 3.3V			
Standard		64 MB	
Maximum		192 MB	
Speed		60ns	
Hyper Page mode memory access		Yes	
Data/Address Bus Width		64bit/32bit	
Local Bus Clock Speed		66 MHz	
BIOS		512KB: 4Mbit FLASH EPROM, 5V	
Supported standards		APM (v.1.2); ACPI w/ACPI-OS; PnP 1.0a; VESA (v2.0); DPMS, DCC2B, SM (v.2.1); PCI BIOS	
SYSTEM MANAGEMENT		SM 2.1 BIOS support with asset tag capability Toshiba Configuration Builder CD supports Microsoft® Windows 98 and Windows 95 Year 2000 Compliance: NSTL Hardware Tested	
VIDEO			
Memory		2.5 MB <i>integrated into chipset</i>	
Speed		50ns	
Hyper Page mode support		Yes	
Controller Chip		Trident Cyber 9525	
Data Bus Width		64-bit	
PCI Local Bus support		Yes: 33MHz, 32-bit	
Graphics Accelerator:		Yes with 64-bit BitBLT support	
2D graphics support		BitBLT, DirectDraw, H/W Cursor, Patterned Fills, Polygon Fill	
3D Supported Features			
Modeling		Fogging, Lighting	
Shading		Flat shading, Gouraud shading	
Rendering		Bilinear texture mapping , Anti-aliasing, MIP mapping, Z-buffering (16-bit or 32-bit)	
Alpha-blending		Yes	
Direct3D support		Yes	
Digital Video Accelerator:		Yes	
YUV-to-RGB color space conversion		Yes	
Scaling/Interpolation/Zoom		Yes	
Internal Support			
	Resolution	<u>Colors Support</u>	
(Full Screen)	1024 x 768	64K colors	
Smaller Image	640 x 480	16.7M colors	
Smaller Image	800 x 600	16.7M colors	
Virtual Display Mode	1280 x 1024	256 colors	
EXTERNAL VIDEO SUPPORT		<u>Colors Support</u>	<u>Vertical Refresh Rate (Non-Interlaced)</u>
	Resolution		
	640 x 480	16.7M colors	85/75/65Hz @ 16.7M colors
	800 x 600	16.7M colors	85Hz @ 16.7M colors
	1024 x 768	64K colors	85 Hz @ 64K colors
	1280 x 1024	256 colors	60 Hz @ 256 colors

SATELLITE 4090XDVD Product Specifications

MODEL	PART NUMBER	DESCRIPTION
4090XDVD	PAS409U-T2DW8	Intel® Celeron® 400MHz, 14.1" TFT , 64MB, 6.4bb HDD , Modem, DVD-ROM Windows 98 w/ dual linked Win95/98 Configuration Builder CD
4090XDVD-NT	PAS409U-T2DN4	Intel® Celeron® 400MHz, 14.1" TFT , 64MB, 6.4bb HDD , Modem, DVD-ROM Windows NT Configuration Builder CD (CB Pro Compatible)

DISPLAY	
Type	TFT Active Matrix Color
Resolution	1024 x 768
Size	14.1" Diagonal
Dot Pitch	.279mm x .279mm
Contrast Ratio	100:1 (Min)

ALL-IN-ONE DESIGN

STORAGE	
Removable HDD (2.5" Enhanced IDE)	6.4 billion bytes (13msec)
Buffer	512KB Buffer
Removable	Service-removable
Height	9.5mm or 8.5mm
Burst Data Transfer Rate	Ultra DMA Mode 2 (33.3MB/s); PIO Mode 4 (16.7MB/s)
FDD (3.5" 1.44MB; 12.7mm high)	Yes
Simultaneous FDD & CD-ROM Support	Yes: two independent units

DVD-ROM		<u>DVD-ROM</u>	<u>CD-ROM</u>
Type	Toshiba SD-C2102		
Height	12.7mm		
Weight	0.62 lbs.		
Operation modes			
Rotational Speed		2.4X Max	20X Max
Random Access Time		160ms	110ms
Sustained Data Transfer rate		1352-2,704 KB/sec	1290-3,000 KB/sec
CD-ROM Compatibility	CD-ROM, CD-R, CD-RW (read only)		
DVD-ROM Compatibility	DVD-ROM only (no DVD-RAM supported)		
DVD-Movie compatibility	Region 1 (North America). <i>(Not supported under Windows NT).</i>		

SOUND SYSTEM		Toshiba Sound System
Chipset		ESS ES1978S (PCI audio accelerator)
16-bit stereo audio playback/record		Yes
Maximum sampling rate		48 kHz
FM Synthesis support		64-channel wavetable music synthesis
Full duplex function		Yes
Sound formats supported:		SoundBlaster Pro™, .WAV, MIDI
Speaker system		Stereo Bass-Reflex speaker system
Form factor		Two top-mounted stereo speakers (28mm, 8 Ω) <i>with volume control</i>

INTERNAL MODEM		Integrated V.90/K56flex modem
DAA support		US/Canada and Europe
Data support		
	Protocols supported	Bell-103/212A, CCITT-V.21/V.22, V.32, V.32bis, V.34, V.90
	Error correction	MNP 1-4
	Data compression	MNP 5, CCITT V.42 bis
Fax support		Fax class 1
	Protocols supported	V.21 ch2, V.27 ter, V.29, V.17
Modem Functions		
Standard software		RingZero® RingCentral™ telephony software
Supported Functions		Ring Wake-up Resume

SATELLITE 4090XDVD Product Specifications

MODEL	PART NUMBER	DESCRIPTION
4090XDVD	PAS409U-T2DW8	Intel® Celeron® 400MHz, 14.1" TFT , 64MB, 6.4bb HDD , Modem, DVD-ROM Windows 98 w/ dual linked Win95/98 Configuration Builder CD
4090XDVD-NT	PAS409U-T2DN4	Intel® Celeron® 400MHz, 14.1" TFT , 64MB, 6.4bb HDD , Modem, DVD-ROM Windows NT Configuration Builder CD (CB Pro Compatible)

KEYBOARD

84 keys, 3mm Travel	Yes
Keyboard Height	8mm
Key Pitch	19.05mm
Key support	Windows 95/98, Application support
Dedicated function keys	12 dedicated function keys
Cursor control (8 Keys, Inverted "T")	Yes
Numeric keypad (Integrated Overlay)	Yes

EXPANSION SLOTS

Two Stacked PC Card Slots	Yes: Holds two - 5mm PC Cards Type II or one - 10.5mm PC Card Type III.
Support Standards	Yes: Supports 32-bit, 3.3V PC CardBus cards <i>and</i> 16-bit, 5.0V PC card standards
Internal Memory Slot (One only)	Yes

EXPANSION PORTS

Expansion Bus	Yes
One 9-Pin Serial (16550 UART equivalent)	Yes
One 25-Pin Parallel (8 bit ECP)	Yes
One 15-Pin RGB (SVGA video)	Yes
Fast Infrared port (Back only)	Yes: IrDA 1.1:4Mbps compatible
One (PS/2) 101 Keyboard/Mouse port	Yes: "Y" connector supported
Universal Serial Bus (USB) port	Yes: Supports 127 devices. Throughput Rate: 12Mbits/sec.
Microphone (3.5mm mini jack, stereo)	Yes
Headphone (3.5mm mini jack, stereo)	Yes
Line-in (3.5mm mini jack, stereo, 2V rms)	Yes
One Noteworthy security lock port	Yes
One RJ-11 jack	Yes

POWER

Autosensing External AC Adapter	Part#: PA2450U
Dimensions/Weight	4.9"L x 2.46"W x .97"H --- Weight: .66lbs.
Input (Voltage/Frequency)	100-240V; 50-60Hz
Output (Voltage/Amps)	15 VDC; 3.0A
Power Output (Watts)	45W
Battery Type: Li-Ion	(4000mAH; 10.8V) -- one standard: Part# PA2487URG
Battery Life: (Full Power)	2.5+ hrs.
Recharge Time (Computer Off/On)	2.8 hrs. <i>depending on the computer function performed</i>
Power Saving Features	APM v.1.2 BIOS, CPU Sleep mode, HDD Auto Off, Auto Resume, Display Auto Off CPU speed change, Hibernation

DIMENSIONS

	<u>Dimensions</u>	<u>Weight</u>
Notebook	12.2"W x 10.2"D x 1.6"H	7.0 lbs.
AC Adapter	6.9"L x 2.8"W x 0.7"H	.85lbs.
Battery (Standard)	6.87"L x 2.76"W x 0.73"H	.88 lbs.

SATELLITE 4090XDVD Product Specifications

MODEL	PART NUMBER	DESCRIPTION
4090XDVD	PAS409U-T2DW8	Intel® Celeron® 400MHz, 14.1" TFT, 64MB, 6.4bb HDD , Modem, DVD-ROM Windows 98 w/ dual linked Win95/98 Configuration Builder CD
4090XDVD-NT	PAS409U-T2DN4	Intel® Celeron® 400MHz, 14.1" TFT, 64MB, 6.4bb HDD , Modem, DVD-ROM Windows NT Configuration Builder CD (CB Pro Compatible)

BUNDLED SOFTWARE (Windows 98 Models)

Windows® 98, Toshiba Utilities (HWSetup, Quick Hibernation, Power Saver, Hotkey Utility, Toshiba Hibernation Utility), Fn-esse™
Mediamatics DVD Express, Intel Indeo Video, AT&T WorldNet Service, RingZero® RingCentral™, America Online update,
Symantec Norton® Antivirus™ Scanner, User's Guide

CD's Included: Bootable Dual linked Win95/98 Configuration Builder CD (Configuration Pro Compatible) & Companion Diskette

For Windows 98 Models Only

Customer Choice Software: Select of a Total of 5 Additional Software Titles. Pay only \$6.95 shipping

Office Productivity

*Lotus® SmartSuite Millenium Edition (counts as 5 selections): Lotus 123, Approach, Freelance Graphics, Wordpro, and Organizer
Dragon Point & Speak™ (requires the purchase of a \$6.00 microphone)*

Mobile Productivity

Laplink® 7.5	Print Artist™ 4.5
Rand McNally TripMaker® 1999	Snapshot
USA 99: Streets & Destinations	

Education

The Way Things Work 2.0	Encyclopedia of Science 2.0
Eyewitness Children's Encyclopedia	Higher Score Guaranteed ACT/SAT/PSAT
Math Blaster™ Algebra	Jump Start Family Activity CD

Entertainment

You Don't Know Jack™ Movies	Asteroids
Sierra Sports™ Ski Racing '99	Battlezone
OddWorld: Abe's Oddysee™	Jack Nicklaus 5.0
Total Annihilation™	

BUNDLED SOFTWARE (Windows NT Models)

Windows NT 4.0, Windows NT Service Pack 4.0, Toshiba Windows NT4.0 Utilities, User's Guide, Microsoft Internet Explorer

CD's Included: Windows NT Configuration Builder CD (CBCD) Pro Compatible & Toshiba Companion Diskette

SECURITY	Hardware	Cable Lock slot & PC Card lock slot. By screw only: HDD & internal modem
	Password	Power-on, Supervisor, & HDD password
	Miscellaneous	Screen blank, keyboard lock

WARRANTY 1 YR Parts / 1 YR. Labor / 1 YR. Battery

ENVIRONMENTAL SPECIFICATIONS

	<u>Operating</u>	<u>Non-operating</u>
Temperature:	41°F (5°C) to 95°F (35°C)	-4°F (-20°C) to 149°F (65°C)
Thermal Gradient: 20° C per hour (max.)	N/A	N/A
Relative Humidity	20% to 80% non-condensing	10% to 95% non-condensing
Altitude	-197 to 9,843ft. (-60 to 3000m)	-197 to 32,808ft. (-60 to 10,000m)
Shock	10G (11ms)	60G (66ms)
Vibration	0.5G	1G