

PIXMA iP100 Photo Printer

Item Code: 1446B002

Specifications

Printer

| | |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Printer Type | Photo Printer |
| Print Speed (up to) | Black: Up to 20 ppm (as fast as 3.0 seconds per page) ² Color: Up to 14 ppm (as fast as 4.3 seconds per page) Postcard Size: 4" x 6" borderless photo: approx. 50 seconds |
| Number of Nozzles | Nozzles: Black:320 Color:1,536 Total:1,856 |
| Print Resolution (Up to) | Black: 600 x 600 dpi ¹ Color: 9600 x 2400 dpi ¹ |
| OS Compatibility | Windows Vista™, Windows XP/2000 and Mac OS® X v.10.3.9 to 10.5.x ⁷ |
| Standard Interface | PictBridge (Cable not included) ⁵ , USB 2.0 Hi-Speed, IrDA, Bluetooth® v2.0 + EDR ⁴ (optional) |
| Noise Level (Approx.) | 38.5 dB(A) in the best quality mode |
| Physical Dimensions | 12.7"(W) x 2.4"(H) x 7.2"(D) |
| Weight | 4.4 lbs. |
| Power Consumption | 9W (1.5W Standby) |
| Warranty | Toll-free technical phone support plus 1 year limited warranty with InstantExchange program. ⁸ |
| Software Included | CD-ROM including Printer Driver, Setup Software and User's Guide, Easy-PhotoPrint EX |

[▲ Back to top](#)

1. Resolution may vary based on printer driver setting. Color ink droplets can be placed with a horizontal pitch of 1/9600 inch at minimum.
2. Print speed measured as soon as first page begins to feed into printer. Output speed will vary depending upon a

number of factors. See www.usa.canon.com/printspeed for additional information.

3. Requires mobile phone or other device with IrDA port and the phone positioned no more than 7.9 inches from the printer. Bluetooth operation depends on the devices and software used. Operating distance is approximately 10 meters but may vary due to obstacles, radio signals, locations where radio interference occurs, magnetic fields from microwave ovens, device sensitivity and/or antenna performance.
4. Bluetooth v2.0 with optional Canon Bluetooth Unit BU-30. Bluetooth operation depends on the devices and software version used. Operating distance is approximately 10 meters but may vary due to obstacles, radio signals, locations where radio interference occurs, magnetic fields from microwave ovens, device sensitivity and/or antenna performance.
5. Requires mobile phone equipped with PictBridge technology and a USB cable.
6. Specifications are subject to change without notice. All printer images and effects are simulated.
7. System requirements vary by application.
8. Warranty programs are subject to certain conditions and restrictions. See www.canontechsupport.com for details.

† Prices and specifications subject to change without notice. Actual prices are determined by individual dealers and may vary.