



- 2.0 Megapixel Digital Photography
- Touch Screen Control via LCD screen
- 1600 x 1200 Resolution
- 4X Digital Zoom
- Secure Digital® (SD) Memory Cards
- Changeable Face Plates
- USB Digital Interface



PDR-T10
Digital Still Camera

PDR-T10

Digital Still Camera



At 2 million pixels, it's picture perfect fun!

The fun and easy-to-use Toshiba PDR-T10 is the first digital camera to utilize its LCD as an interactive touch-screen menu for operation of camera functions... no buttons, no toggles, it works with a stylus! Plus it's the only digital camera with interchangeable faceplates, so you can change its look to fit your mood — from zebra skin to grasshopper green! On the performance side, the fully automatic PDR-T10 matches its beauty with a smart 2.0 megapixel CCD sensor that captures brilliant color photographs at resolutions up to 1600 x 1200 in universal JPEG format. You'll benefit from the all-glass 4X digital zoom lens with macro for unbelievable close-ups, stunning portraits and landscapes, or just capturing your everyday fun. Plus, with its USB connection, it could not be easier or faster to download your photos to your computer.



Compression settings to suit your needs.

The PDR-T10 gives you the choice of three compression levels.

- High: for standard shooting requirements
- Standard: in cases where emphasis lies in the image quality
- Economy: when shooting quantity is most important



CCD
 • 1/2.7 inch CCD
 • 2.0 million pixels

Resolution
 • 1600 x 1200,
 800 x 600

File Format
 • JPEG

Recording Medium
 • Secure Digital® (SD)
 • Compatible to 256MB

Lens
 • Aperture: F3.1/F8
 • f=5.96mm,
 f= 38@35mm
 • 5 elements in 4 groups,
 all glass
 • 4X Digital Zoom

Focus
 • Automatic, Manual

White Balance
 • Automatic, Daylight,
 Cloudy, Incandescent,
 Fluorescent 1 and 2,

Program AE
 • Yes

Scene Selected
 • 6 modes, Sports, Night,
 Auto, Macro, Portrait,
 Landscape

Metering
 • Center

Shutter Speed
 • 1-1/500 sec.

Sensitivity
 • Equivalent to ISO
 100/200/400

Monitor
 • 1.6 inch TFT
 (61K pixels)

Playback Modes
 • Zoom 4x, Single
 Frame, Slide Show,
 Thumbnail

Flash
 • Auto, red eye reduction,
 off, fill-in flash,
 slow-sync

Flash Range
 • 0.4m to 2.0m

Self-Timer
 • Yes (2/10 sec)

DCF Format
 • Yes

Digital Interface
 • USB

Power
 • 1 CR-V3 or 2 AA
 Lithium or Nickel-Metal
 Hydride

Battery Life
 • 200 shots based on
 bundled CR-V3 battery

AC Adapter
 • Sold separately
 PDR-AC20

Auto Power Off
 • Yes: 1, 2, 3 minutes


Dimensions (WxHxD)
 • 3.36" x 2.83" x 1.1"
 • Weight: 4.2 ounces

Epson® PRINT™ Image
 • Yes

Accessories
 • 8MB SD® Card, 1 CR-
 V3 battery, USB Cable,
 Hand Strap with Stylus
 Pen, Camera Bag, Two
 Faceplates, CD-ROM
 with ImageExpert
 Software, USB
 Driver, Instruction
 Manual

INTERCHANGEABLE FACEPLATES

Choose from a wide selection of interchangeable faceplates to personalize your camera. Faceplates are sold in sets of four (PDR-KFP1, PDR-KFP2).



SECURE DIGITAL® CAPACITY

of shots - High/Standard Mode: 1600 x 1200; Economy Mode: 800 x 600

	HIGH MODE	STANDARD MODE	ECONOMY MODE
8MB	6	12	51
16MB	14	28	106
32MB	30	59	224
64MB	62	122	460
128MB	126	248	931
256MB	253	495	1854

The recording data amount is not fixed due to the subject, so the number of frames does not necessarily follow the table.

