

ViewSonic® G90F 19" PerfectFlat® Multimedia Monitor

Specification:

| | | |
|-------------------|---------------------------|--|
| CRT | Size | 19" (18" VIS) |
| | Dot Pitch | 0.21 Horizontal, 0.14 Vertical, 0.25 Diagonal |
| | Maximum Resolution | 1600 X 1200 |
| | Glass Surface | Anti-glare, anti-static, SuperClear |
| INPUT SIGNAL | Video | RGB Analog (75 ohms, 0.71 Vp-p) |
| | Sync | H/V separate (TTL) composite |
| | Frequency | Fh: 30-97kHz, Fv: 50-180Hz |
| COMPATIBILITY | PC | PC compatible from VGA up to 1600 x 1200 |
| | Mac | Power Mac™ compatible up to 1600 x 1200 |
| CONNECTOR | Signal | 15-pin mini D-sub |
| | Power | 3-pin plug (IEC320) |
| POWER | Voltage | AC 90-132V / 198-264VAC (auto switch) AC, 50-60(+/-3)Hz |
| | Consumption | 120W (typ) |
| USER CONTROLS | Basic | Power, ON/OFF, menu, down, up, enter |
| | On Screen Display | Contrast, brightness, H/V-position, H/V-size, pincushion, trapazoid, pin-balance, parallelogram, tilt, top/bottom hook control, degauss, H/V moire reduction, language, ViewMatch color, H/V focus adjustment, ViewMeter ® ,OSD function, recall |
| VIDEO INPUT | Bandwidth | 200MHz |
| DIMENSIONS | Physical | H: 18.3"/465mm W: 17.6"/448mm D: 18.1"/459mm |
| WEIGHT | Net | 22kg (48.5lb) |
| SPECIAL FEATURES | | Flat Screen |
| EMISSION STANDARD | | TCO'99 |
| POWER MANAGEMENT | | Meets ENERGY STAR®, VESA ®DPMS, TCO '99 and Energy 2000 standards |
| WARRANTY | | Three year limited warranty on CRT, parts and labor. 48 hour Express Exchange ® service option available. |