

TOSHIBA

Toshiba Pocket PC e750/e755

<u>Model</u>	<u>Part number</u>	<u>Description</u>
e750	PD750U-0001Q	Intel®PXA255 400MHz/3.8", 240x320 TFT, 32MB(ROM)-64MB(RAM), 32MB NAND(Flash ROM Disk), SD, CFII, Microsoft Pocket PC 2003
e755	PD750U-0001QR	Intel®PXA255 400MHz/3.8", 240x320 TFT, 32MB(ROM)-64MB(RAM), 32MB NAND(Flash ROM Disk), SD, CFII, Microsoft Pocket PC 2003, ArcSoft PhotoBase

Product Highlights

- Providing a generous 96MB (64MB RAM/32MB NAND) of storage capacity, Pocket PC e750 users can easily access data and multimedia files with the touch of a finger. For added peace of mind, critical files stored in NAND memory will remain intact even if the PDA battery runs down.
- With integrated Wi-Fi (IEEE 802.11b) wireless connectivity, Pocket PC e750 users can remain flexible and check e-mail and view files from the company network and conveniently surf the Web at any local "hotspot". With an optional headset, users can enjoy hands free VoIP (voice over IP) communication (requires additional software).*
- Whether indoors or outdoors, Pocket PC e755 users can view their favorite images or Web sites with the large, crisp 3.8" diagonal transreflective color display
- Featuring the power-saving Intel PXA255 processor, the Pocket PC e750 delivers added performance to quickly access your files and programs while consuming less power.
- Providing the user a variety of expansion capabilities, the Pocket PC e750 features dual integrated Secure Digital™ and CompactFlash II™ expansion slots and optional accessories including an Expansion Pack, high capacity battery, thumbpad keyboard and a foldable keyboard.

System Characteristics

Processor

- Intel® PXA255 processor at 400MHz

Memory

- 64MB SDRAM
- 32MB CMOS Flash ROM
- Application Memory: 32MB NAND Memory (Flash ROM Disk)

Graphics/Video

- 3.8" TFT Transreflective Color display; 240 x 320 (portrait) resolution (16 bit)
- Back light LED
- 65,536 (64K) colors: 5 step brightness control (by Software)
- ATI Graphics Controller; 384KB internal video memory
- Support Resolution/Color (VGA): QVGA 320 x 240 (RGB (Monitor) via Expansion Pack)
External Resolution:
640 x 480 64K colors @60Hz
800 x 600 64k colors @60Hz

Input Devices

- **Touch Panel:** Analog resistance sensitive system touch panel
- **Controls/Buttons:** 5-way navigation button; 4 application keys- Calendar, Contacts, Task, Menu; 3 function navigator (Toshiba Scroller) for Up, Down and Action; Reset switch; Voice record button; Power on/off button; Battery on/off switch; Wireless communication switch, Stylus pen

Expandability

- 1 Type I/Type II CF Card Slot (3.3V)
- 1 SD (Secure Digital) card slot (3.3V)

Communications

- Integrated Wi-Fi (IEEE 802.11b) *

Ports

- RGB (Monitor) port (**via Expansion Pack**)
- Universal Serial Bus port – Host via Expansion Pack
- Infrared port (115kpbs)
- DC-in
- Cradle connector port (26 pins)
- Stereo headphone/Microphone port (Stereo; 4 ring jack 3.5mm)

Physical Description

- Dimensions (LxWxH): 4.9" x 3.1" x 0.6"
- Weight: 6.9oz

- LED Indicators: Power Charging/Alarm; Wireless LAN Power

Sound

- AC-97 Codec Chip; WM9705 Sound Chip
- 16-bit stereo; 44.1KHz Max Sample Rate
- Full Duplex support
- Software Volume Control (by Software)
- Built-in Microphone and Built-in Speaker

Power Supply

- **AC Adapter:** 5V/2A DC output; 100-240V input voltage, 50/60Hz frequency
- **Battery Pack:** Rechargeable, replaceable Advanced Lithium-Ion (Li-Ion) battery; 3.7V x 1000mAh
Rechargeable, replaceable Advanced Li-Ion back-up battery; 3000mAh
- Battery Saver: Stand by; Display Auto Off

Battery life may vary depending on applications, power management settings and features utilized. Recharge time varies depending on usage.

Operating System

- **Microsoft® Pocket PC 2003**

Additional Software

- Pocket Word
- Pocket Excel
- Pocket Outlook®
- Pocket Internet Explorer
- Microsoft® Reader for Pocket PC
- Microsoft® Windows® Media™ Player 9 for Pocket PC
- File Explorer
- MSN® Messenger
- Microsoft® Transcriber
- Microsoft® Active Sync® 3.7
- Microsoft® Outlook
- IA Presenter for ATI
- IA Screen Mirror for ATI
- ArcSoft® PhotoBase™ for Pocket PC (Toshiba Pocket PC e755 only)

Warranty

- 1 year parts, labor and battery
- 90-day limited warranty on operating system and applications

Environmental Specifications

- **Temperature:** Operating: 0 to 40°C ; Storage: -20 to 65°C
- **Relative Humidity:** 30% to 80%
- **Altitude (relative to sea level):** Operating: 10,000ft, change rate 2000ft/min; Storage: 40,000ft, change rate 2000ft/min

SelectServ® Warranty Programs

SWC-HEQE2V	2 Year Next Business Day Exchange
SWC-HEGE2V	2 Year SystemGuard + Next Business Day Exchange
SWP-HEQE3V	3 Year Next Business Day Exchange
SWP-HEGE3V	3 Year SystemGuard + Next Business Day Exchange

Accessories

Toshiba Accessories

Power

PA1309U-1PPS	Power/Sync Cable
PA3183U-1ACA	10W AC Adapter
PA3186U-2DST	USB Cradle w/AC Adapter
PA3261U-1CHG	Battery Charger w/AC Adapter
PA3197U-1BRL	Toshiba High Capacity Battery (3000 mAh)
PA3187U-1BRS	Toshiba Primary Battery

Expansion

PA3243U-1ETC	Toshiba Pocket PC USB Host Cable
PA3188U-1PRP	Toshiba Expansion Pack
PA3271U-1BTM	Toshiba SD Bluetooth II

— More

Memory

SD-M3203B3	32MB Secure Digital (SD) Card
SD-M6403B3	64MB Secure Digital (SD) Card
SD-M1283B3	128MB Secure Digital (SD) Card
SD-M2564B3	256MB Secure Digital (SD) Card

Input Devices

F8A1500	Belkin Foldable Keyboard
NW780U	Targus Click N' Type (Thumb input Device)
PA3182U-1ETC	Stylus Pen (3-Pack)

Cases

PA1301U-2PCS	Leather Holster
PA1307U-1PCS	Leather Universal
PA1308U-1PCS	Leather Organizer
PA1313U-1PCS	Leather Universal Plus
	Accommodates e750 w/optional High Capacity Battery and Expansion Pack
550325T	Kenneth Cole Leather Case- Large

Other

PA1322U-1PMS	Screen Overlays
--------------	-----------------

Product/Part Numbers

Pocket PC e750	PD750U-0001Q
Pocket PC e755	PD750U-0001QR

* Note: Subscription of an Internet Service Provider is necessary for Internet connection