

TOSHIBA

Satellite® 1410/1415 Series

Great Features and Performance at a great price

Model(s):

Satellite 1415-S173

Cel 1800MHz/15.0" TFT/256MB/30GB/DVD-CDRW/Mdm/LAN/WinXP Home

Satellite 1410-S173

Cel 1800MHz/15.0" TFT/256MB/30GB/DVD-CDRW/Mdm/LAN/WinXP Pro

Satellite 1415-S174

Cel 1800MHz/15.0" TFT/256MB/30GB/DVD-CDRW/Mdm/LAN/WinXP Pro

Satellite 1410-S174

Cel 1800MHz/15.0" TFT/256MB/30GB/DVD-CDRW/Mdm/LAN/Win XP Home

Part Numbers

PS141U-01F3WV

PS141U-01F3W7

PS141U-01F3W6

PS141U-01F3W3

Product Highlights

Performance

- Intel® Celeron® processor 1.80GHz
- 256MB expandable to 512MB

All-in-one design

- 30GB* hard disk drive
- DVD-ROM/CDRW multi-function drive
- 3.5" 1.44MB floppy diskette drive

Great Features

- 15.0" TFT active matrix display
- NVIDIA GeForce4 420 Go graphics controller with 16MB video memory

Get On-Line

- Integrated V.92/56K modem
- Integrated 10/100 Ethernet LAN
- *Optional Upgrade:* Integrated 802.11b Wireless capabilities

System Characteristics

CPU

- Intel® Celeron® processor 1.80GHz*
- Integrated co-processor

L2 Cache

- 256KB Level 2 Cache integrated in module
- 400MHz front side bus clock speed

Memory

- 256MB expandable to 512MB; SODIMM expansion memory
- 128/256MB PC1600 SDRAM, 2.5V
- Data/Address Bus Width; 64-bit/13-bit
- BIOS ROM: 4Mbit, Intel FWH
- Intel 845MZ Chipset

Mass Storage

- **Floppy Disk Drive:** 3.5", 1.44MB
- **Primary Hard Disk Drive:** 30GB* hard disk drive; Enhanced IDE (ATA-5); 9.7mm height, 14.3ms average access time (read/write), 3ms track to track seek time (read/write), supports PIO mode4, Ultra DMA mode5, Multiword DMA mode2, service removable
- **DVD-ROM/CDRW:** Enhanced IDE (ATAPI Interface); Compatibility: CD-ROM, CD-R (read/write), CD-RW (read/re-write), DVD-ROM, DVD-R (read only), supports PIO mode4, Multiword DMA mode2, Ultra DMA mode2
- Software Decoder: WinDVD

Graphics/Video

- 15.0" TFT active-matrix display; Internal display supports up to 16M colors at 1024 x 768
- NVIDIA GeForce4 420 Go graphics controller; 16MB internal video memory
- 3D Graphics Accelerator, AGP bus support; 2D Graphics Accelerator, BitBLT hardware, Hardware cursor, DirectDraw support
- External Color Support/Refresh rate:
800 x 600; 60/75/85/100Hz Non-Interlaced @16M
1024 x 768; 60/75/85/100Hz Non-Interlaced @16M
1280 x 1024; 60/75/85/100Hz Non-Interlaced @16M

1600 x 1200; 60/75/85/100Hz Non-Interlaced @16M
1920 x 1440; 60/75Hz Non-Interlaced @16M
2048 x 1536; 60Hz Non-Interlaced @16M

- **Keyboard:** Full sized 85 keys with 12 function keys, 2.7mm key stroke, 6mm height; Dedicated Windows® & Application keys support; HotKey function; **TouchPad** pointing device; Scroll function (by help of driver)
- **CD Control Function:** Play/Pause, Stop/Eject, Previous, Skip/Next, CD Power
- Instant Access Internet Button
- Toshiba Console Button

Expandability

- 2 Expansion memory slot (including main memory slot); 2 PC Card slots support 2 Type II or 1 Type III PC Cards; 32-bit CardBus ready

Communications

- Integrated V.92/56K modem; Data and fax support
 - Integrated 10/100 Ethernet LAN
 - *Optional Upgrade:* Integrated Wireless LAN (IEEE 802.11b)
- Due to FCC limitations, speeds of 53kbps are the maximum permissible transmission rates during Download. Actual data transmission speeds will vary depending on line conditions.

Ports

- ECP Parallel printer port
- RGB Port (Monitor)
- 3 Universal Serial Bus ports
- TV-Out (NTSC/PAL output; RCA jack)
- RJ-45 LAN port
- RJ-11 modem port

Physical Description

- Dimensions (LxWxH): 12.8" x 11.2 x 1.7"
- Weight: 7.8lbs
- LED Indicators: Power, Power Save Mode, HDD, FDD, CD/DVD-ROM, DC-IN, Caps Lock, Arrow, Numeric, Main Battery Charging Status, System Sleep / Suspend status

Sound

- YMF753 Codec Chip; Software Sound Chip
- 16-bit stereo, Built-in stereo speakers
- Direct 3D Sound; DirectSound (supported by driver) and DirectMusic; Full Duplex and MIDI support
- Sound Volume Control Dial
- **Ports:** Microphone port, headphone port

Power Supply

- **AC Adapter:** 75W external AC Adapter, 100-240V / 50-60Hz frequency (Universal) input voltage, 15V x 5A Output.
Dimensions (LxWxH): 5.5" x 2.2" x 1.1" "
Weight: 0.88lbs
- **Battery Pack:** 9-cell, rechargeable, removable Li-Ion battery, 10.8V x 4500mAh = 48.6Wh
Dimension (LxWxH): 6.8" x 2.7" x 0.7"
Weight: 0.8 lbs
- Up to 2.52H battery life; Recharge time (off/on): 3H/4H-11H+
Battery life may vary depending on product model, configuration, applications, power management settings and features utilized.

Recharge time varies depending on usage. Battery may not charge while computer is consuming full power. After a period of time, the battery will lose its ability to perform at maximum capacity and will need to be replaced. This is normal for all batteries. To purchase a new battery pack, see the accessories information that shipped with your computer or visit www.accessories.toshiba.com

Satellite 1415-S173 (Win XP Home)	PS141U-01F3WV
Satellite 1410-S173 (Win XP Pro)	PS141U-01F3W7
Satellite 1415-S174 (Win XP Pro)	PS141U-01F3W6
Satellite 1410-S174 (Win XP Home)	PS141U-01F3W3

* GB = 1 billion bytes

Security

- Slot for computer lock, Main Battery Pack (sliding lock), HDD and memory (by screw only), Built-in Modem/LAN (screw only), User Power-on password, Setup Security, HDD Password, Keyboard Lock (by Hotkey), Screen Blank (by Hotkey), Screen Saver by software

Bios

- TSETUP, APM, ACPI, PhP, VESA, DPMS, DDC, SM BIOS, PC BIOS support

Operating System

- **Microsoft® Windows XP Home (1415-S173 & 1410-S174)** pre-installed
- **Microsoft® Windows XP Pro (1410-S173 & 1415-S174)** pre-installed
- Windows 2000 component drivers on the web

Additional Software

- Microsoft® Works (1415 models only)
- Intuit Quicken Basic 2001
- Norton AntiVirus 2002
- AOL (3 –Month offer)
- Adobe Acrobat Reader
- AT&T Worldnet® Service – 1 Month Free
Telephone access and other charges and other terms and conditions may apply. Offer available to new customers only. Offer expires 4/30/04.
- Microsoft Internet Explorer
- Toshiba Custom Utilities
- Satellite Series Online Documentation
- **Toshiba Great Software Offer:** Receive your choice of two software titles. The software selection includes titles from the follow categories; productivity, education/reference, creativity and entertainment

Warranty

- 1 year parts, labor and battery

Environmental Specifications

- **Temperature:** Operating: 5° to 35°C (41° to 95°F); Non-operating: -20° to 65°C (-4° to 149°F)
- **Thermal gradient:** Operating: 15°C per hour maximum; Non-operating: 20°C per hour maximum
- **Relative Humidity:** Operating: 20% to 80% non-condensing; Non-operating: 10% to 95% non-condensing
- **Altitude (relative to sea level):** Operating: -60 to 3000 meters; Non-operating: -60 to 10,000 meters
- **Shock:** Operating: 10G; Non-operating: 50G
- **Vibration:** Operating: 0.1G; Non-operating: 1.0G

Accessories

Toshiba Accessories

PA3083U-1ACA	75W Universal AC adapter
PA3107U-1BRS	Li-Ion Battery Pack
PA2488U	Battery Charger

Cases (Targus)

NWCTM1	Metropolitan Carrying Case (koskin)
PA450U	Targus Defcon Key Lock

Kingston Memory

KTT3614/128	128MB PC2100 SDRAM Memory
KTT3614/256	256MB PC2100 SDRAM Memory

Wi-Fi (Agere)

8484415560	Wireless LAN PC Card (Gold)
7000011030	AP-2000 (802.11a/b) Access Point
8485878380	AP-500 (802.11b) Access Point

* Central Processing Unit ("CPU") Performance Disclaimer:

CPU performance in your computer product may vary from specifications under the following conditions:

- use of certain external peripheral products
- use of battery power instead of AC power
- use of certain multimedia games or videos with special effects
- use of standard telephone lines or low speed network connections
- use of complex modeling software, such as high end computer aided design applications
- use of computer in areas with low air pressure (high altitude >1,000 meters or >3,280 feet above sea level)
- use of computer at temperatures outside the range of 5°C to 35°C (41°F to 95° F) or >25°C (77°F) at high altitude (all temperature references are approximate).

CPU performance may also vary from specifications due to design configuration.

Under some conditions, your computer product may automatically shut-down. This is a normal protective feature designed to reduce the risk of lost data or damage to the product when used outside recommended conditions. To avoid risk of lost data, always make back-up copies of data by periodically storing it on an external storage medium. For optimum performance, use your computer product only under recommended conditions. Read additional restrictions under "Environmental Conditions" in your product Resource Guide. Contact Toshiba Technical Service and Support for more information.


Return Policy

TAIS does not accept the return of component parts, or bundled software, which have been removed from the PC system. Pro-rata refunds on individual PC components or bundled software, including the operating system, will not be granted. If you wish to return a complete PC system, contact the TAIS dealer where you purchased the product, and comply with the dealer's standard return policies and procedures.


Product/Part Numbers/UPC

Toshiba America Information Systems Inc. ("TAIS") shall not be liable for damages of any kind for use of this information, which is subject to change without notice. Copyright 2002 TAIS portables_satellite_1410S173.doc Created on 10/2/2002 4:57 PM Page 2 of 2


Front with display open




Front with display closed




Left side




Right side



Back



Underside



*Wi-Fi Mini PCI module is optional