



productivity



cost savings

data sheet



hp LaserJet 3300mfp series
3300mfp • 3320mfp • 3320n mfp • 3330mfp

HP LaserJet 3300mfp printer copier scanner fax series provides efficient, reliable HP LaserJet performance, versatile copying, color scanning and business class faxing. They distribute and print documents efficiently and effectively without sacrificing valuable office space.

improved productivity

- improved productivity—one efficient multifunction device improves communications processes for small businesses by combining print, copy, scan and fax functions
- integrated functions—print, copy, scan and fax in one device, supports multi-tasking, saves space and reduces costs in your PC or Macintosh® environment
- save time—instant-on fuser, 15 pages-per-minute engine and automatic document feeder deliver fast efficient printing and copying
- leverage the power of the Internet—digital sending features convert paper documents to PDF e-mail attachments in a few easy steps
- low intervention—duty cycle of 10,000 pages-per-month plus optional high-capacity hp microfine print cartridges easily support multiple users in a busy small office

hp LaserJet simplicity and reliability

- high-quality documents—a high-resolution, 1200 dpi laser print engine with true resolution enhancement technology creates crisp, clear professional looking documents
- hp LaserJet engineering—printing, copying, scanning and faxing, with the reliability and efficiency you expect from hp, enables individual users to concentrate on getting their work done instead of tending their equipment
- worry-free—easy set-up, easy-to-handle supplies and reassuring one-year warranty make this mfp the right choice for businesses without large IT resources

greater flexibility

- easy to use—enhanced control panel functions for convenient walk-up copying and faxing
- versatile design—legal-size flatbed document glass, color scanner and automatic feeder make it easy and fast to copy and scan a wide variety of originals
- easy to share—hp jetdirect 310x Fast Ethernet print server provides easy sharing, simple network installation, and compatibility with a wide range of network environments
- independent functions—receive or send faxes, scan or copy without waiting for print jobs to finish

HP printing and imaging systems help you create powerful, professional communications easily. Printers, supplies, accessories and services that are designed together to work together and invented to meet your business needs.

hp LaserJet 3300mfp series

hp LJ3330mfp printer-copier-scanner-fax shown

business class faxing at 3 seconds per page

50-sheet automatic document feeder makes copying and scanning big jobs fast and easy

easy-to-use front-panel copy/scan/fax buttons and 2-line LCD screen

one-touch speed dials and additional fax functions

full-function copy control panel

scan-to-email, scan-to-OCR, scan-to-archive functions

large, flatbed color scanner handles a variety of originals up to legal size

hp jetdirect 310x Fast Ethernet print server for easy sharing within a small workgroup (standard with LJ3320n mfp)

USB and parallel connections can connect two computers simultaneously

125-sheet output tray

32 MB RAM standard for storing fax pages or printing complex documents

straight-through paper path for custom media

10-sheet priority feed tray for letterhead, cover sheets and easy media versatility

250-sheet input tray supports even big jobs with less user intervention

enhance your business communications

- quickly convert paper documents to PDF e-mail attachments and then send them to any e-mail address in a few easy steps
- cost-saving alternative to fax charges or courier services
- document is scanned in color, the recipient of the email receives a near-original quality document
- user scans a document into the integrated OCR application which converts the document to an editable and digitally storable Word file
- archive paper-based documents electronically with one-touch scan-to-archive function

printer

- 15 pages per minute
- first page out in less than 10 seconds
- 1200 by 1200 dpi resolution

flatbed copier

- up to 14 copies per minute
- 600 by 600 dpi resolution
- automatic collation
- reduce/enlarge features (25 percent to 200 percent)

color scanner

- 600 ppi resolution
- high fidelity color
- scan-to-email
- scan-to-OCR
- scan-to-archive

fax

- G3/33.6 Kbps modem faxes documents at 3 seconds per page
- stores up to 220 pages
- quick dialing for up to 275 speed dial numbers

hp LaserJet 3300mfp

- 15 pages-per-minute printing
- flatbed legal-size scan glass
- color scanning
- 250-sheet input paper tray
- 125-sheet output paper tray
- 32 MB memory

hp LaserJet 3320mfp

all the features of the 3300mfp plus:

- 50-page automatic document feeder speeds up large copy and scan jobs

hp LaserJet 3330mfp

all the features of the 3320mfp plus:

- business-class faxing capabilities
- stores up to 275 speed dials
- receive faxes to PC for privacy
- daisy chain upstream answering machine

hp LaserJet 3320n mfp

all the features of the 3320mfp plus:

- hp jetdirect 310x Fast Ethernet external print server makes this mfp network-ready right out of the box
- hp network printer wizard makes connecting to your network fast and easy

cost savings

return on investment

HP multifunction products are 20–40% less expensive than the combined costs of single-function products plus they help you save valuable office space by consolidating the full complement of single function products into just one footprint. And the cost savings don't stop there—the HP LaserJet 3300mfp series simplifies your office environment by allowing you to maintain, support, and service fewer devices. Now you can print, copy, scan, fax and digitally send documents at one reliable device—increasing your users' productivity while saving you time and money.

ease of use

The HP LaserJet 3300mfp series was designed to be your reliable, hassle-free multi-tasking device with low intervention rates, simple maintenance and easy-to-use one-touch functions on the control panel. With an mfp that is built on a reliably engineered HP LaserJet engine, you can count on uninterrupted performance and high-quality print, copy and fax documents. HP Ultraprecise print cartridges have been designed to produce extraordinarily high-quality results that provide the clarity needed for halftone images, smooth grayscales and fine details. The all-in-one print cartridge allows users to easily change supplies and continue printing, copying and faxing quickly. Plus, the HP one-year express exchange warranty and award-winning HP Customer Care service and support options allow you to concentrate on your business, not your equipment.

hp LaserJet experience

HP's renowned LaserJet reliability and networking expertise is at the base of every HP LaserJet mfp. For best-in-class quality, reliability, manageability and performance, HP is the only choice—PC Magazine gives "A" ratings to HP year after year.

print, copy, scan, digitally send, fax

With the HP LaserJet 3300 series, you have the luxury of getting up to five different devices in one machine. With one multifunction product delivering everything from printing, copying, scanning, digital sending and faxing, you only have one set of consumables to stock, one set of instructions to learn and one set of software to load—and with the easy, reliable HP Jetdirect networking option, everyone in your small workgroup receives the benefits of enhanced productivity.

- High-quality, fast printing with media flexibility—plain paper, transparencies, envelopes and cardstock from 3-by-5 inches to 8.5-by-14 inches.
- With convenient walk-up copying capabilities, intuitive control panel and flatbed design, this mfp is a true replacement for your analog copier.
- Versatile flatbed, color scanning that can copy just about any kind of original up to legal size.
- Independent functionality allows users to receive or send faxes, scan or copy without waiting for print jobs to finish—and if one independent function goes down, the others still work.
- Digital sending that leverages the power and speed of the Internet to enhance your office communications.
- Convert paper documents into PDF email attachments that can be quickly sent to any email address or use the Optical Character Resolution (OCR) capabilities to convert paper documents into editable, electronically storable digital files.
- Robust, fast business-class faxing without having to purchase, connect and maintain a separate device.
- Daisy chain upstream devices, such as an answering machine, with distinctive ring detect.

reliability

technical specifications

hp LaserJet 3300mfp series

32 MB memory
Expandable to 96 MB through one DIMM slot
66 MHz processor
10,000 pages-per-month duty cycle
IO ports: 1 parallel, 1 USB

print

Up to 15 pages per minute (letter); 10-second first page out
Resolution: 1200 by 1200 dpi (True Resolution Enhancement Technology)
Print margins: left/right: 0.23 in (6.0 mm); top/bottom: 0.20 in (5.08 mm)
Printer languages: PCL 5e, PCL 6, PostScript® Level 2 emulation

copy

Up to 14 copies per minute (letter)
Resolution: 600 x 600 dpi enhanced with edge detection technology
50-sheet automatic document feeder (ADF)—standard with LJ3320mfp, LJ3320n mfp, LJ3330mfp
1–99 copies with automatic collation
Copy reduction and enlargement: 25% to 200%

scan

Color and monochrome scanning
Scanner compatibility: TWAIN 1.7
Resolution: 600 ppi color
ReadIRIS Pro OCR v6.0
Scannable area:
Minimum size: 2 by 3.5 in (51 by 89 mm)
Maximum size: 8.5 by 14 in (216 by 356 mm)
Send and print job overlap

fax

Storage: 220 pages
Resolution: standard, fine, superfine
Transmission speed: 3 seconds-per-page with 33.6 Kbps modem
Fax compatibility: Super G3 (IUT Group 3); ECM
Quick dialing: up to 275 speed dials, 225 group dial numbers,
10 one-touch front panel keys
Distinctive ring detect
Ability to daisy chain upstream devices (i.e. answering machines)

control panel

Fax, copy, scan, and print control buttons
Two-line text display
Alpha-numeric and numeric keypads

paper handling

Input trays:
250-sheet input tray, 30 envelopes
10-sheet priority input tray
Straight thru paper path
50-sheet automatic document feeder
Output tray: 125-sheet output capacity

media types and sizes

Media type: paper, envelopes, transparencies, labels, cardstock, custom media
Media sizes: letter, legal, no. 10 envelopes, Monarch envelopes, and sizes 3-by-5 inches to 8.5-by-14 in (76-by-127 mm to 126-by-356 mm)
Media weights: up to 42 lb

font capabilities

45 scalable TrueType™ fonts, 35 PostScript

minimum system requirements

Windows® 95 (basic functions only) and 98: Pentium® 90 with 16 MB RAM
Windows Me: Pentium 150 with 32 MB RAM
Windows NT® 4.0: Pentium 90 with 32 MB RAM
Windows 2000: 133 MHz processor with 64 MB RAM
180 MB free hard disk space for Windows; 160 MB for Macintosh, Macintosh OS 9.1 and X
CD ROM drive
USB port or dedicated IEEE 1284-compliant bi-directional parallel port
Line Printer Daemon (LPD)

connectivity

Two hot ports
Bi-directional IEEE 1284-compliant parallel port
USB 2.0

networking

HP Jetdirect 310x external print server—standard with LJ3320n mfp, optional to other models
HP Jetdirect 380x external wireless print server—optional, connects to standard 802.11b wireless networks

environmental ranges

Operating temperature: 59 to 90.5° F (15 to 32.5° C)
Storage temperature: -4 to 104° F (-20 to 40° C)
Operating humidity: 10 to 80% RH non-condensing
Storage humidity: 0 to 95% RH non-condensing

acoustics

Operating position: LpAm = 58 dB printing, LpAm = 39 dB idle/Powersave
Bystander position: LpAm = 49 dB printing, LpAm = 36 dB idle/Powersave
Sound Power: LwAd = 6.4 Bels printing, LwAd = 5.1 Bels idle/Powersave
Tests per ISO 9296 (ISO 7779)

ordering information

number	description
C9124A	HP LaserJet 3300mfp digital printer-copier-scanner
C9125A	HP LaserJet 3320mfp digital printer-copier-scanner with automatic document feeder
C9151A	HP LaserJet 3320n mfp network ready digital printer-copier-scanner with automatic document feeder
C9126A	HP LaserJet 3330mfp digital printer-copier-scanner-fax with automatic document feeder
service and support	
H5471A/E	HP Supportpack—3-year, next-day exchange
H5478A/E	HP Supportpack—3-year, next-day onsite
accessories	
C9143A	Automatic document feeder
memory	
C7842A	8 MB SDRAM DIMM
C7843A	16 MB SDRAM DIMM
C7845A	32 MB SDRAM DIMM
Q1887A	64 MB SDRAM DIMM
interface and cables	
C2946A	Parallel cable, 3-meter IEEE-1284 A to C
C2947A	Parallel cable, 10-meter IEEE-1284 A to C
C6518A	USB cable, 2-meter A to B
supplies	
print cartridges	
C7115A	HP Ultraprecise print cartridge, 2,500 pages
C7115X	HP Ultraprecise print cartridge, 3,500 pages
media	
92296T	HP LaserJet monochrome transparency, 50 sheets, letter
HP11124	HP LaserJet paper, 500 sheets, letter
HPM1120	HP Multipurpose paper, 500 sheets, letter
network	
J6038A	HP Jetdirect 310x Fast Ethernet external print server (USB)
J6061A	HP Jetdirect 380x 802.11b Wireless external print server (USB)
J6062A	HP Jetdirect wp110 802.11b Wireless external print server (parallel)

power requirements

Source: Input voltage 100 to 127 volts (±10%); 220 to 240 volts (±10%)
Frequency: 50 or 60 Hz (±2 Hz)

power consumption

Printing (continuous): 330 watts maximum
Standby (ready state): 41 watts
Powersave: 14 watts
Off mode: 0 watts
ENERGY STAR® compliant

product certification

UL and cUL listed to UL 1950/CSA 950; complies with IEC 950/EN 60950; meets Class A limits for FCC Part 15 and CISPR 22; product CDRH-certified Class 1 Laser Product (safe for office/EDP use)

dimensions (w by d by h)

LJ3300mfp: 21.5 by 20.5 by 16.5 in (546 by 521 by 419 mm)
LJ3320mfp, LJ3320n mfp, LJ3330mfp: 21.5 by 20.5 by 19.5 in (546 by 521 by 495 mm)

weight

LJ3300mfp: 31 lb (14.1 kg); LJ3320mfp, LJ3320n mfp, LJ3330mfp: 34.6 lb (15.8 kg)

warranty

One-year limited express exchange

what's in the box

Product; print cartridge, power cord; getting started guide; support flyer; product software and product user guide CD-ROM; 250-sheet media input tray, priority input tray; ADF input tray (except LJ3300mfp); fax guide; phone cord (LJ3330mfp only); HP Jetdirect 310x external print server (LJ3320n mfp only)

For more information on the HP LaserJet 3300mfp, visit our Web site at www.hp.com and click on products and services. Here you will find information on products, supplies, and accessories for all your computing needs. HP peripherals, personal computers, supplies, and accessories are available at authorized HP resellers worldwide.

HP PCs use genuine Windows Operating Systems www.microsoft.com/piracy/howtotell

For more information

Product: Visit www.hp.com/go/mfp

Purchase: HP business solutions, products and supplies can be purchased at your local HP partner (www.hp.com/go/locator), or bought directly from HP at www.buy.hp.com or 800-613-2222.

Finance: HP finance plans provide all the benefits of new technology without the risk or cost of ownership. For details, call toll-free 888-999-HPTF (4783).

Accessibility: HP is committed to providing products and services that are accessible to people with disabilities. For more information, please visit www.hp.com/accessibility or call 888-259-5707.

ENERGY STAR is a U.S. registered service mark of the United States Environmental Protection Agency. As an ENERGY STAR partner, HP has determined that this product meets the guidelines for energy efficiency. Microsoft, MS-DOS, Windows, and Windows NT are U.S. registered trademarks of Microsoft Corporation. Netscape is a U.S. trademark of Netscape Communications Corporation. PostScript is a trademark of Adobe Systems Incorporated. TrueType is a U.S. trademark of Apple Computer, Inc. The information contained in this document is subject to change without notice. HP makes no warranty of any kind with respect to this information. HP specifically disclaims the implied warranty of merchantability and fitness for a particular purpose. HP shall not be liable for any direct, indirect, incidental, consequential, or other damage alleged in connection with the furnishing or use of this information.

