

Satellite A500 Detailed Product Specification¹

Model Name: A500-ST5605	Part Number: PSAT0U- 010001	UPC: 883974335091
--------------------------------	------------------------------------	--------------------------

Operating System ^{C1} 2

- Genuine Windows[®] 7 Home Premium 64-bit

Processor³ and Graphics⁴

- Intel[®] Core™ 2 Duo processor T6600
 - 2.20GHz, 2MB L2 Cache, 800MHz FSB
- Mobile Intel[®] GM45 Express Chipset
- Intel[®] Graphics Media Accelerator 4500MHD with 128MB-1759MB dynamically allocated shared graphics memory

Memory⁵

- Configured with 4GB DDR3 800MHz (max 8GB)

Storage Drive⁶

- 400GB (5400 RPM) Serial ATA hard disk drive

Fixed Optical Disk Drive⁷

- DVD SuperMulti drive supporting 11 formats
 - Maximum speed and compatibility: CD-ROM (24x), CD-R (24x), CD-RW (24x), DVD-ROM (8x), DVD-R (Single Layer, (8x)), DVD-R (Double Layer, (6x)), DVD-RW (6x), DVD+R (Single Layer, (8x)), DVD+R (Double Layer, (6x)), DVD+RW (8x), DVD-RAM (5x)

Display⁸

- 16.0" diagonal widescreen TruBrite[®] TFT LCD display at 1366x768 native resolution (HD)
 - Native support for 720p content

Sound

- Built-in harman/kardon[®] stereo speakers

Input Devices

- 104 key US keyboard with 10-key
- TouchPad™ pointing device with multi-touch control
- TouchPad™ Enable/Disable button
- Media Control Buttons:
 - eco utility button (Energy-saving mode)
 - Mute
 - Media
 - CD/DVD control buttons
 - Volume up, volume down

Communications

- Webcam and microphone
- Modem⁹
- 10/100 Ethernet
- Realtek[®] 802.11b/g/n wireless LAN¹⁰

Expandability

- 2 main memory slots. Both slots may be occupied.
- ExpressCard™ slot (ExpressCard/34 and ExpressCard/54)
- Memory Card Reader
 - Secure Digital, Secure Digital High Capacity, Memory Stick™, Memory Stick PRO™, Multi Media Card, xD Picture Card [shared slot]

	Operating	Non-operating
Temperature ¹⁶	5° to 35° C	-20° to 60° C
Relative Humidity (non-condensing)	20% to 80%	10% to 90%
Thermal Gradient	15° C per hour (max)	20° C per hour (max)
Altitude (relative to sea level)	0 to 3,000 meters	0 to 10,000 meters
Shock	10G	60G
Vibration	0.5G	1.0G

Ports

- Video
 - RGB (monitor) output port
 - HDMI-CEC
- Audio
 - S/P DIF output port (shared with headphone port)
 - Microphone input port
 - Headphone output port
- Data
 - 4 USB v2.0 ports
 - 3 x USB v2.0 ports
 - 1 x eSATA/USB combo port with USB Sleep and Charge¹¹
 - RJ-45 LAN port
 - RJ-11 modem port
- Security
 - Slot for Security Lock

Physical Description

- Fusion™ Finish with Sonic Pattern in Black Onyx
- Dimensions (W x D x H): 15.1" x 10.2" x 1.44"/1.61"
- Weight: Starting at 6.48 lbs., depending upon configuration¹²

Battery¹³

- 4000 mAh (6 cell) Lithium Ion battery pack

Power Supply

- 90W (19V x 4.74A) Auto-sensing , 100-240V/50-60Hz AC Adapter
- Dimensions (W x D x H): 5.2" x 2.3" x 1.2"
- Weight: starting at .81 lbs.

Software ^{C1} 14

- Toshiba Software and Utilities
 - Electronic User's Guide
 - Bluetooth Stack for Windows by Toshiba
 - TOSHIBA Recovery Media Creator
 - TOSHIBA ConfigFree[®]
 - TOSHIBA Disc Creator
 - TOSHIBA DVD Player
 - TOSHIBA Power-saving eco utility
 - TOSHIBA Hard Drive Impact Sensor (3D sensor)
 - TOSHIBA Face Recognition
 - TOSHIBA PC Health Monitor
 - Hard Disc Drive (HDD) Recovery
- Third-party Software
 - Microsoft[®] Windows Media Player
 - Microsoft[®] Works 9
 - Internet Explorer 8
 - Adobe[®] Acrobat[®] Reader
 - Google™ Toolbar
 - Dolby[®] Sound Room[®]
 - Corel[®] DVD MovieFactory[®] for TOSHIBA
 - Sun[®] Java™ 2 Runtime Environment
 - WildTangent[®] Orb™ Game Console
- Trial Software
 - Norton Internet Security™ 2009, 30-day trial
 - Microsoft[®] Office Home and Student 2007 Edition, 60-day trial
- Special Offers
 - Toshiba Online Backup
 - NetZero[®] Internet Service
 - Skype[®]
 - Intuit[®] Quickbooks[®] Financial Center

Environmental Specifications

- This product is RoHS¹⁵ compatible
- Energy Star 5.0 Qualified
- EPEAT™ Gold Compliant

1 YEAR STANDARD LIMITED WARRANTY¹⁷

- Includes International Limited Warranty for obtaining service when traveling outside the United States.

Service Upgrades and Extensions

Toshiba offers many different enhanced services such as SystemGuard®, On-Site Repair, and ServiceExpress to provide additional support to your notebook PC. For a full description and complete list of programs and program terms and conditions, please visit www.pcsupport.toshiba.com.

Accessories

For additional and most updated accessories, please visit www.accessories.toshiba.com

Memory Upgrade

Part Number	Description
PA3669U-1M2G	Toshiba 2GB DDR2-800 Memory Module
PA3670U-1M4G	Toshiba 4GB DDR2-800 Memory Module

Power

Part Number	Description
PA3717U-1ACA	Toshiba 120W Global AC Adapter
PA3534U-1BRS	Toshiba Primary Li Ion Battery Pack (6 cell)
PA3727U-1BRS	Toshiba Primary High Capacity Li Ion Battery Pack (12 cell)

Expansion

Part Number	Description
-------------	-------------

PA3575U-1PRP	dynadock USB Docking Station with DVI/VGA port
PA3579U-1ETC	Toshiba Universal Notebook/Projector Stand

Storage

Part Number	Description
PA3556U-1M2G	Toshiba 2GB USB Hi-Speed Flash Drive, ReadyBoost
PA3556U-1M4G	Toshiba 4GB USB Hi-Speed Flash Drive, ReadyBoost
PA3556U-1M8G	Toshiba 8GB USB Hi-Speed Flash Drive, ReadyBoost
HDDR320E04XW	Toshiba External USB Hard Drive, 320GB (White)
HDDR500E04XL	Toshiba External USB Hard Drive, 500GB (Blue)
HDDR640E04XR	Toshiba External USB Hard Drive, 640GB (Red)

Protection

Part Number	Description
PA3611U-1ETC	Toshiba Keyboard Protector

Bluetooth

Part Number	Description
PA3573U-1ETA	Toshiba Bluetooth Optical Tilt-Wheel Mouse (Black/Silver)
PA3573U-1ETB	Toshiba Bluetooth Optical Tilt-Wheel Mouse (Black/Red)

Carrying Case

Part Number	Description
PA1446U-1CS6	Toshiba 16" Envoy Ballistic Polyester Carrying Case (Fits up to 16")
PA1448U-1RS6	Toshiba 16" Envoy Roller Case (Fits up to 16")

Subject to Change

While Toshiba has made every effort at the time of publication to ensure the accuracy of the information provided herein, product specifications, configurations, prices, system/component/options availability are all subject to change without notice. For the most up-to-date product information about your computer, or to stay current with the various computer software or hardware options, visit Toshiba's Web site at <http://www.pcsupport.toshiba.com>

Return Policy

Notwithstanding anything to the contrary in any third party License Agreement or product documentation supplied with your PC, Toshiba America Information Systems, Inc. ("TAIS") does not accept the return of component parts, or bundled software, that have been removed from the PC system. Pro-rata refunds on individual PC components or bundled software, including the operating system, will not be granted. If you wish to return a complete PC system, contact the TAIS dealer where you purchased the product, and comply with the dealer's standard return policies and procedures.

Toshiba America Information Systems, Incorporated ("TAIS")
9740 Irvine Boulevard
Irvine CA 92618

ToshibaDirect website: <http://www.toshibadirect.com>
TAIS website for resellers: <http://sell.toshiba.com>
TAIS PC Support website: <http://pcsupport.toshiba.com>

Satellite, ConfigFree and SystemGuard are registered trademarks of Toshiba America Information Systems, Inc. and/or Toshiba Corporation. All other products and names mentioned are the property of their respective owners.

64-bit computing:

64-bit computing requires that the following hardware and software requirements are met:

- 64-bit Operating System
- 64-bit CPU, Chipset and BIOS (Basic Input/Output System)
- 64-bit Device drivers
- 64-bit applications

Certain device drivers and/or applications may not be compatible with a 64-bit CPU and therefore may not function properly. See "Detailed Specs" for more information.

¹ **Product Series Legal Footnote.** The product specifications and configuration information are designed for a product Series. Your particular model may not have all the features and specifications listed or illustrated. For more detailed information about the features and specifications on your particular model, please visit Toshiba's Web site at pcsupport.toshiba.com.

Product Offering Legal Footnote. Toshiba America Information Systems, Inc. reserves the right to modify or withdraw this offer at anytime without notice

² **Operating System.** Also see **64-Bit Computing** Legal Footnote, if applicable.

Certain Microsoft® software product(s) included with this computer may use technological measures for copy protection. IN SUCH EVENT, YOU WILL NOT BE ABLE TO USE THE PRODUCT IF YOU DO NOT FULLY COMPLY WITH THE PRODUCT ACTIVATION PROCEDURES. Product activation procedures and Microsoft's privacy policy will be detailed during initial launch of the product, or upon certain reinstallations of the software product(s) or reconfigurations of the computer, and may be completed by Internet or telephone (toll charges may apply).

Some software may differ from its retail version (if available), and may not include user manuals or all program functionality.

Offers. Offer terms, duration and product availability all subject to change without notice

³ **Processor (Central Processing Unit).** Also see **64-Bit Computing** Legal Footnote, if applicable.

CPU performance in your computer product may vary from specifications under the following conditions:

1. use of certain external peripheral products
2. use of battery power instead of AC power
3. use of certain multimedia, computer generated graphics or video applications
4. use of standard telephone lines or low speed network connections
5. use of complex modeling software, such as high end computer aided design applications
6. use of several applications or functionalities simultaneously
7. use of computer in areas with low air pressure (high altitude >1,000 meters or >3,280 feet above sea level)
8. use of computer at temperatures outside the range of 5°C to 30°C (41°F to 86°F) or >25°C (77°F) at high altitude (all temperature references are approximate and may vary depending on the specific computer model – please visit the Toshiba website at www.pcsupport.toshiba.com for details).

CPU performance may also vary from specifications due to design configuration.

Under some conditions, your computer product may automatically shut-down. This is a normal protective feature designed to reduce the risk of lost data or damage to the product when used outside recommended conditions. To avoid risk of lost data, always make back-up copies of data by periodically storing it on an external storage medium. Use your computer product only under recommended conditions. Read additional restrictions under "Environmental Conditions" in your product "Detailed Specs." Contact Toshiba Technical Service and Support for more information.

⁴ **Graphics (Graphics Processing Unit).** GPU performance may vary depending on product model, design configuration, applications, power management settings and features utilized. GPU performance is only optimized when operating in AC power mode and may decrease considerably when operating in battery power mode.

Total Available Graphics Memory is the total of, as applicable, Dedicated Video Memory, System Video Memory and Shared System Memory. Shared System Memory will vary depending on system memory size and other factors.

⁵ **Memory (Main System).** Part of the main system memory may be used by the graphics system for graphics performance and therefore reduce the amount of main system memory available for other computing activities. The amount of main system memory allocated to support graphics may vary depending on the graphics system, applications utilized, system memory size and other factors. Computers configured with a 32-bit operating system can address up to 3GB of system memory. Only computers configured with a 64-bit operating system can address 4 GB or more of system memory.

⁶ **Storage Drive (Internal HDD Capacity).** One Gigabyte (GB) means $10^9 = 1,000,000,000$ bytes and One Terabyte (TB) means $10^{12} = 1,000,000,000,000$ bytes using powers of 10. The computer operating system, however, reports storage capacity using powers of 2 for the definition of $1\text{ GB} = 2^{30} = 1,073,741,824$ bytes and $1\text{ TB} = 2^{40} = 1,099,511,627,776$ bytes, and therefore shows less storage capacity. Available storage capacity will also be less if the computer includes one or more pre-installed operating systems, such as Microsoft Operating System and/or pre-installed software applications, or media content. Actual formatted capacity may vary.

⁷ **Optical Drive.** Due to manufacturing and quality variations in third party optical media (e.g., CD or DVD) or optical media players/recorders, in certain cases, your Toshiba optical drive may not record on certain optical media that bear the applicable logo, or playback optical media recorded by other PCs or optical media recorders. Additionally, certain optical media recorded on your optical drive may not playback or operate properly on other PCs or optical media players. These problems are not due to any defect in your Toshiba PC or optical drive. Please refer to your PC's product specification for listing of specific format compatibilities.

Recording or viewing of certain optical media may be limited or prevented in accordance with applicable copy protection standards.

⁸ **Display.** Small bright dots may appear on your screen display when you turn on your PC. Your display contains an extremely large number of thin-film transistors (TFT) and is manufactured using high-precision technology. Any small bright dots that may appear on your display are an intrinsic characteristic of the TFT manufacturing technology. Over a period of time, and depending on the usage of the computer, the brightness of the screen will deteriorate. This is also an intrinsic characteristic of the screen technology. When the computer is operated on battery power, the screen will dim and you may not be able to increase the brightness of the screen while on battery power.

⁹ **Modem Speed.** Due to FCC limitations, speeds of 53 kbps are the maximum permissible transmission rates during download. Actual data transmission speeds will vary depending on line conditions.

¹⁰ **Wireless-N.** The wireless adapter is based on a draft release version of the IEEE 802.11n specification, and may not be compatible with, or support all features (e.g., security) of, certain Wi-Fi® equipment.

¹¹ **USB Sleep & Charge.** The "USB Sleep & Charge function" may not work with certain external devices even if they are compliant with the USB specification. In those cases, turn the power of the computer ON to charge the device.

¹² **Weight.** Weight may vary depending on product configuration, vendor components, manufacturing variability and options selected.

¹³ **Battery Life.** Battery life may vary considerably from specifications depending on product model, configuration, applications, power management settings and features utilized, as well as the natural performance variations produced by the design of individual components. Published battery life numbers are achieved on select models and configurations tested by Toshiba at the time of publication. See "Detailed Specs" for specific battery measurement test. Recharge time varies depending on usage. Battery may not charge while computer is consuming full power. After a period of time, the battery will lose its ability to perform at maximum capacity and will need to be replaced. This is normal for all batteries. To purchase a new battery pack, see the accessories information that shipped with your computer or visit the Toshiba web site at www.accessories.toshiba.com.

¹⁴ **Software.** Also see 64-Bit Computing Legal Footnote, if applicable.

Some software may differ from its retail version (if available), and may not include user manuals or all program functionality.

Certain Microsoft® software product(s) included with this computer may use technological measures for copy protection. IN SUCH EVENT, YOU WILL NOT BE ABLE TO USE THE PRODUCT IF YOU DO NOT FULLY COMPLY WITH THE PRODUCT ACTIVATION PROCEDURES. Product activation procedures and Microsoft's privacy policy will be detailed during initial launch of the product, or upon certain reinstallations of the software product(s) or reconfigurations of the computer, and may be completed by Internet or telephone (toll charges may apply).

Microsoft® Office 2007 60-Day Trial Version: This trial software will work for 60 days after you first use it. You will not be able to use the software if you do not activate it as described the first time you use the software. You can activate the software by Internet. Internet service charges may apply. If you want to keep the software after the 60-day trial period, you must convert to the perpetual version. You can convert online by following the conversion instructions presented during setup and paying the required fees.

¹⁵ **RoHS.** This notebook is compatible with European Union Directive 2002/95/EC, Restriction of the use of certain Hazardous Substances in electrical and electronic equipment (RoHS), which restricts use of lead, cadmium, mercury, hexavalent chromium, PBB, and PBDE. Toshiba requires its notebook component suppliers to meet RoHS requirements and verifies its suppliers' commitment to meeting RoHS requirements by conducting component sampling inspections during the product design approval process.

¹⁶ **Temperature (Environmental) Conditions.** All temperature references are approximate and the performance of your computer may vary from specifications even when operating within the recommended temperature range.

¹⁷ **Warranty.** The terms and conditions of Toshiba's standard limited warranty are available at www.warranty.toshiba.com.