

<b>Product Specifications</b>		
Physical ports/indicators on the dynadock:		
TOP	FRONT Panel	BACK Panel
<ul style="list-style-type: none"> <li>• Undock/dock button</li> </ul>	<ul style="list-style-type: none"> <li>• Power LED</li> <li>• Status LED</li> <li>• Two (2) USB 2.0 ports (Sleep and Charge)</li> <li>• 3.5mm Line in (microphone)</li> <li>• 3.5mm Line out (Headphone)</li> </ul>	<ul style="list-style-type: none"> <li>• Wireless USB antennas</li> <li>• Wireless USB on/off switch</li> <li>• 3.5mm Line out (Speakers)</li> <li>• S/PDIF Digital Audio</li> <li>• 10/100 LAN</li> <li>• Four (4) USB 2.0 ports</li> <li>• DVI-I Video Port (DVI to VGA adapter included)</li> <li>• USB in connector (from PC), for initial installation</li> <li>• DC in (power)</li> <li>• Cable lock slot</li> </ul>
<ul style="list-style-type: none"> <li>• Video resolution up to 1680 x 1050 / 1600 x 1200, 16/32-bit color</li> <li>• Supported video modes: Mirror Mode, Extended Mode, Primary Display</li> <li>• On-board Graphic Memory: 16M-Byte DDR SDRAM</li> <li>• EMI Standards Approvals; FCC</li> <li>• Compliance: <ul style="list-style-type: none"> <li>○ Certified Wireless USB (Band Group 1,3,&amp; 6 supported for world-wide use***),</li> <li>○ Certified USB high Speed</li> <li>○ WiMedia Alliance,</li> <li>○ WHQL Windows Vista Premium Logo, USB compliant, RoHS compliant, Toshiba Green Procurement Requirements</li> </ul> </li> </ul>		
<b>Color:</b> Champagne Metallic Opal & Black		
<b>Product Dimensions:</b> 1.7" x 3.1" x 8.7" (w/o base plate)		
<b>Product Dimensions:</b> 4.5" x 5.2" x 9.3" (with base plate)		
<b>Product Weight:</b> 3 lbs 4 oz		
<b>Package Contents:</b> Wireless U docking station, Wireless USB Adapter, base plate, USB 2.0 cable (for connecting dynadock to computer during setup and can be used for wired connectivity), AC power adapter, AC power cord/cable, DVI-I to VGA adapter, CD (user's manual, drivers and utility) and documentations.		
<b>Environmental:</b> RoHS Compliant		
<b>Warranty:</b> One-year limited warranty		

<b>System requirements</b>
<ul style="list-style-type: none"> <li>• 1.2GHz or higher processor. Intel® Pentium®/Celeron® family, or AMD K6®/AMD Athlon™/AMD Duron™ family, or compatible processor recommended (Intel® Core™ 2 Duo 2.0 GB or higher processor recommended for optimal video performance)</li> <li>• 512 MB memory or higher (1 GB memory or higher recommended)</li> <li>• USB 2.0 port</li> <li>• 80MB of available disk space</li> <li>• CD-ROM drive</li> <li>• Embedded wireless USB module or external wireless USB host adapter (wireless USB adapter included in box)</li> </ul> <p><b>Operating System:</b></p> <ul style="list-style-type: none"> <li>• Microsoft® Windows® XP: <ul style="list-style-type: none"> <li>○ Home edition SP2/SP3, Professional edition SP2/SP3</li> </ul> </li> <li>• Microsoft® Windows Vista®</li> </ul>

- o Windows Vista Ultimate, Windows Vista Enterprise, Windows Vista Business, Windows Vista Home Premium, Windows Vista Home Basic, Windows Vista Starter 2007
- o Both 32-bit edition and 64-bit edition
- Microsoft® Windows® 7:
  - o Windows 7 Home Premium, Windows 7 Professional, Windows 7 Ultimate
  - o Windows 7 drivers available from October 22, 2009
- Check [dynadock.com](http://dynadock.com) for all the latest drivers
- Power requirements: Input: AC 100-240V