

Qosmio G45-AV680 Detailed Product Specification¹

Model Name: G45-AV680	Part Number: PQG41U-001001	UPC: 032017912502
------------------------------	-----------------------------------	--------------------------

Operating System ^{C1} 2

- Genuine Windows Vista™ Ultimate (32-bit version)

Processor and Chipset³

Intel® Centrino® Duo processor technology featuring:

- Intel® Core™ 2 Duo Processor T7300⁴
 - 2.00GHz, 4MB L2, 800MHz FSB with 64-bit ^{C1}
- Mobile Intel® PM965 Express Chipset
- Integrated Wi-Fi® compliant wireless LAN
 - Intel® Wireless WiFi Link 4965AGN (802.11a/g/n)⁵

Memory⁶

- Configured with 2048MB PC2-5300 DDR2 SDRAM (both memory slots may be occupied). Maximum capacity 4096MB
- Intel® Turbo Memory
 - 1024MB

Hard Disk Drive⁷

- 320GB using two Serial ATA hard disk drives;
 - Primary + Secondary drive: 160GB + 160GB

Fixed Optical Disk Drive⁸

- HD DVD-R/DVD⁹ SuperMulti (+/- double layer) drive (in one optical drive), supporting 13 formats
 - Maximum speed and compatibility: HD DVD-R(1x), HD DVD-ROM (8x), ,CD-ROM (24x), CD-R (16x), CD-RW (4x), DVD-ROM (8x), DVD-R (4x), DVD+R (4x),DVD-RW (4x), DVD+R (Double Layer (2.4x)), DVD-R (Double Layer (2x)), DVD+RW (4x), DVD-RAM (3x)

Toshiba TV Tuner¹⁰

- TOSHIBA USB HDTV Tuner (External)¹¹:

Display¹²

- 17" diagonal widescreen Ultimate TruBrite®TFT active-matrix LCD display at 1920x1200 native resolution (WUXGA)
 - Supports 1080p content
 - Maximum Brightness Cd/m² - up to 350 Cd/m²
 - Contrast Ratio: 450:1
 - Horizontal Viewing Angle: 140 Degrees
 - Vertical Viewing Angle: 110 Degrees

Graphics¹³

- PCI-Express™ x16 graphics subsystem, featuring:
 - NVIDIA® GeForce™ 8600M GT with 512MB DDR2 discrete graphics memory, plus up to 255MB dynamically allocated shared graphics memory using NVIDIA® TurboCache™ technology.¹⁴
 - Total available shared graphics memory 767MB

Sound

- 1-bit Digital Amplifier
- Four built-in harman/kardon® stereo speakers with built-in subwoofer
- Sound Volume Control Dial
- Built-in microphone

Input Devices

- 86 key US keyboard
- TouchPad™ pointing device
- TouchPad™ Enable/Disable
- Control Buttons:
 - Internet button to launch default browser
 - CD/DVD control buttons (Play/Pause, Stop, Prev Track, Next Track)
- Toshiba Remote Control

Communications

- Webcam and microphone built into LCD bezel
- Modem¹⁵

- 10/100/1000 Ethernet
- Integrated Wi-Fi® compliant wireless:¹⁶
 - Intel® Wireless WiFi Link 4965AGN (802.11a/g/n)⁵
- Bluetooth® version 2.0 plus Enhanced Data Rate (EDR)
- Consumer infrared for remote control

Expandability

- 2 main memory slots. Both slots may be occupied.
- One PCMCIA – Type II/Type I Card Slot
- ExpressCard™ slot (ExpressCard/34 and ExpressCard/54)
- 5-in-1 Bridge Media Adapter
 - Secure Digital, Memory Stick™, Memory Stick PRO™, Multi Media Card, xD Picture Card [shared slots]

Ports

- Video
 - RGB (monitor) output port
 - S-Video output port
 - HDMI output port
- Audio
 - S/P DIF output port (shared with headphone port)
 - Audio line-in
 - Microphone input port
 - Headphone output port
- Data
 - i.LINK(tm) IEEE-1394
 - USB v2.0 – 5 ports
- Security
 - Fingerprint reader

Physical Description

- Dimensions (WxDxH Front/H Rear): 17.4" x 11.8" x 1.5" /1.78" without feet
- Weight: Starting at 10.6 lbs depending upon configuration¹⁷
- LCD Cover Color: Cosmic Black Pearl

Power

- 120W (15V x 8A) 100-240V AC Adapter.
- Dimensions (WxDxH): 2.17" x 5.71" x 1.73"
- Weight: starting at 1.43 lbs

Battery¹⁸

- 7050mAh Lithium Ion battery pack
- Dimensions (WxDxH): 5.55" x 3.86" x 0.80"
- Weight: starting at 1.08 lbs

Software ^{C1} 19

- Toshiba Software and Utilities
 - TOSHIBA Value Added Package
 - Electronic User's Guide
 - Bluetooth Stack for Windows by Toshiba
 - TOSHIBA ConfigFree®
 - TOSHIBA Assist
 - TOSHIBA Security Assist
 - TOSHIBA Disc Creator
 - TOSHIBA Extended Tiles for Windows Mobility Center
 - TOSHIBA Speech System
- Third-party Software
 - TOSHIBA Game Console
 - Microsoft Works Version 8.5
 - Sun® Java™ 2 Runtime Environment
 - Adobe® Acrobat® Reader 8.0
 - InterVideo®WinDVD® 8
 - Google™ Desktop
 - Google™ Toolbar
 - Google Picasa™
 - Yahoo! Music™ Jukebox
 - Ulead® DVD MovieFactory® 5 for TOSHIBA
- Trial Software
 - Microsoft Office Trial Home and Student 2007 Edition (60-day trial)

- o McAfee® Internet Security Suite (30-day trial)
- Special Offers
 - o Microsoft Office Live
 - o Shutterfly digital photo service
 - o Napster® music subscription service
 - o eMusic MP3 music subscription service
 - o VONGOSM internet video download service
 - o ebay®
 - o CNN Pipeline
 - o Skype™ internet communications

Environmental Specifications

	Operating	Non-operating
Temperature ²⁰	5° to 35° C (41° to 95° F)	-20° to 65° C (-4° to 149° F)
Thermal Gradient	15° C per hour (max)	20° C per hour (max)
Relative Humidity (non-condensing)	20% to 80%	10% to 90%
Altitude (relative to sea level)	-60 to 3,000 meters	-60 to 10,000 meters
Shock	10G	60G
Vibration	0.25G	1.0G

- This product is RoHS²¹ compatible

QOSMIO – 1 YEAR STANDARD LIMITED WARRANTY + ON-SITE REPAIR²²

Service Upgrades and Extensions

Toshiba offers many different enhanced services such as SystemGuard®, On-Site Repair, and ServiceExpress to provide additional support to your notebook PC. For a full description and complete list of programs, please visit www.pcsupport.toshiba.com.

Recommended Services

Extended Service Plan

Provides an extended service plan for up to 4 total years from the original notebook purchase date. On-site service will be provided at customer's home or business location (excluding weekends and holidays) to perform the necessary hardware repairs.

Part Number	Description
WSN-QEQH2V	2nd Year Extended Service Plan + On-Site Repair
WSN-QEQH3V	2nd/3rd Year Extended Service Plan + On-Site Repair
WSN-QEQH4V	2nd/3rd/4th Year Extended Service Plan + On-Site Repair

SystemGuard Accidental Damage Service²³

Provides advanced protection from damage caused from handling. On-site service will be provided at customer's home or business location (excluding weekends and holidays) to perform the necessary hardware repairs.

Article I. Subject to Change

While Toshiba has made every effort at the time of publication to ensure the accuracy of the information provided herein, product specifications, configurations, prices, system/component/options availability are all subject to change without notice. For the most up-to-date product information about your computer, or to stay current with the various computer software or hardware options, visit Toshiba's Web site at <http://www.pcsupport.toshiba.com>

Article II. Return Policy

Notwithstanding anything to the contrary in any third party License Agreement or product documentation supplied with your PC, Toshiba America Information Systems, Inc. ("TAIS") does not accept the return of component parts, or bundled software, that have been removed from the PC system. Pro-rata refunds on individual PC components or bundled software, including the operating system, will not be granted. If you wish to return a complete PC system, contact the TAIS dealer where you purchased the product, and comply with the dealer's standard return policies and procedures.

Toshiba America Information Systems, Incorporated ("TAIS")
9740 Irvine Boulevard
Irvine CA 92618

ToshibaDirect website: <http://www.toshibadirect.com>

TAIS website for resellers: <http://sell.toshiba.com>

TAIS PC Support website: <http://pcsupport.toshiba.com>

Extended Service Plan included except with 1 Year plan. SystemGuard coverage must be purchased within the first 30 days of notebook purchase.

Part Number	Description
WSN-QEGH2V	1st/2nd Year + Extended Service Plan + On-Site Repair
WSN-QEGH3V	1st/2nd/3rd Year + Extended Service Plan + On-Site Repair
WSN-QEGH4V	1st/2nd/3rd/4th Year + Extended Service Plan + On-Site Repair

Accessories

For additional and most updated accessories, please visit www.accessories.toshiba.com

Memory Upgrade

Part Number	Description
PA3512U-1M1G	Toshiba 1GB DDR2-667 Memory Module
PA3513U-1M2G	Toshiba 2GB DDR2-667 Memory Module

Power

Part Number	Description
PA3237U-3ACA	Toshiba 120W Global AC Adapter
PA3475U-1BRS	Toshiba Primary Li Ion Battery Pack (9 cell)
PA3091U-2CHG	Toshiba Battery Charger w/Integrated AC Adapter)

Expansion

Part Number	Description
PA3541U-2PRP	dynadock USB Docking Station with video port (VGA)
PA3542U-2PRP	dynadock USB Docking Station with video port (DVI)

Security & Protection

Part Number	Description
PA3567U-1ETC	Toshiba Keyboard Protector - 14"-15, 17" NBs (A4 size)
PA410U	Targus DEFCON CL Cable Lock

Storage

Part Number	Description
PA3109U-3FDD	Toshiba USB Floppy Disk Drive Kit
PA1411U-1M1G	Toshiba 1GB USB Hi-Speed Flash Drive
PA1412U-1M2G	Toshiba 2GB USB Hi-Speed Flash Drive

Wireless/Bluetooth

Part Number	Description
PA3573U-1ETA (Black/Silver)	Toshiba Wireless Mouse w/Bluetooth Technology
PA3573U-1ETB (Black/Red)	Toshiba Wireless Mouse w/Bluetooth Technology

Portégé, Satellite, Tecra, SelectBay, ConfigFree and SystemGuard are registered trademarks and Qosmio and EasyGuard are trademarks of Toshiba America Information Systems, Inc. and/or Toshiba Corporation. Intel, Celeron, Centrino, Intel Inside, Pentium, the Intel Centrino logo, and the Intel Inside logo are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Microsoft and Windows are registered trademarks and OneNote registered is a trademark of Microsoft Corporation in the United States and/or other countries. Winstone® is a registered trademark and BatteryMark™ is a trademark of Ziff Davis Publishing Holdings Inc. in the U.S. and other countries. MobileMark™ is a trademark of the Business Applications Performance Corporation. Wi-Fi is a registered certification mark of the Wi-Fi Alliance. The Bluetooth word mark and logos are owned by the Bluetooth SIG, Inc. and any use of such marks by Toshiba is under license. NVIDIA and GeForce are registered trademarks or trademarks of NVIDIA Corporation in the United States and/or other countries. All other trademarks are the property of their respective owners.

^{C1} **64-bit computing:**

64-bit computing requires that the following hardware and software requirements are met:

- 64-bit Operating System
- 64-bit CPU, Chipset and BIOS (Basic Input/Output System)
- 64-bit Device drivers
- 64-bit applications

Certain device drivers and/or applications may not be compatible with a 64-bit CPU and therefore may not function properly. A 32-bit version of the operating system is preinstalled on your computer unless explicitly stated that the operating system is 64-bit. See "Detailed Specs" for more information.

¹ **Product Series Legal Footnote.** The product specifications and configuration information are designed for a product Series. Your particular model may not have all the features and specifications listed or illustrated. For more detailed information about the features and specifications on your particular model, please visit Toshiba's Web site at pcsupport.toshiba.com.

Product Offering Legal Footnote. Toshiba America Information Systems, Inc. reserves the right to modify or withdraw this offer at anytime without notice.

² **Operating System.**

Also see **64-Bit Computing** Legal Footnote, if applicable.

Certain Microsoft® software product(s) included with this computer may use technological measures for copy protection. IN SUCH EVENT, YOU WILL NOT BE ABLE TO USE THE PRODUCT IF YOU DO NOT FULLY COMPLY WITH THE PRODUCT ACTIVATION PROCEDURES. Product activation procedures and Microsoft's privacy policy will be detailed during initial launch of the product, or upon certain reinstallations of the software product(s) or reconfigurations of the computer, and may be completed by Internet or telephone (toll charges may apply).

Some software may differ from its retail version (if available), and may not include user manuals or all program functionality.

Offers. Offer terms, duration and product availability all subject to change without notice

³ **Processor (Central Processing Unit).**

CPU performance in your computer product may vary from specifications under the following conditions:

1. use of certain external peripheral products
2. use of battery power instead of AC power
3. use of certain multimedia, computer generated graphics or video applications
4. use of standard telephone lines or low speed network connections
5. use of complex modeling software, such as high end computer aided design applications
6. use of several applications or functionalities simultaneously
7. use of computer in areas with low air pressure (high altitude >1,000 meters or >3,280 feet above sea level)
8. use of computer at temperatures outside the range of 5°C to 30°C (41°F to 86°F) or >25°C (77°F) at high altitude (all temperature references are approximate and may vary depending on the specific computer model – please visit the Toshiba website at www.pcsupport.toshiba.com for details).

CPU performance may also vary from specifications due to design configuration.

Under some conditions, your computer product may automatically shut-down. This is a normal protective feature designed to reduce the risk of lost data or damage to the product when used outside recommended conditions. To avoid risk of lost data, always make back-up copies of data by periodically storing it on an external storage medium. Use your computer product only under recommended conditions. Read additional restrictions under "Environmental Conditions" in your product "Detailed Specs." Contact Toshiba Technical Service and Support for more information.

⁴ **Core™ 2 Duo Processor**

Intel® Dual Core Technology is a new technology designed to deliver improved performance to the notebook PC. Performance or compatibility may vary. For more information on Intel's Core 2 Duo processors, visit: <http://www.intel.com/core2duo/>. See 64-Bit Computing Legal Footnote, if applicable.

⁵ **Wireless-N.** The Intel® Wireless Wi-Fi® Link 4965AGN (802.11a/g/n) adapter is based on a draft release version of the IEEE 802.11n specification, also known as "Draft-N", which may not be compatible with, or support all features (e.g., security) of, certain Wi-Fi® equipment.

⁶ **Memory (Main System).** Part of the main system memory may be used by the graphics system for graphics performance and therefore reduce the amount of main system memory available for other computing activities. The amount of main system memory allocated to support graphics may vary depending on the graphics system, applications utilized, system memory size and other factors. For PC's configured with 4 GB of system memory, the full system memory space for computing activities will be considerably less and will vary by model and system configuration.

⁷ **Hard Disk Drive (HDD) Capacity.**

1 Gigabyte (GB) means $10^9 = 1,000,000,000$ bytes using powers of 10. The computer operating system, however, reports storage capacity using powers of 2 for the definition of 1 GB = $2^{30} = 1,073,741,824$ bytes, and therefore shows less storage capacity. Available storage capacity will also be less if the product includes one or more pre-installed operating systems, such as Microsoft Operating System and/or pre-installed software applications, or media content. Actual formatted capacity may vary.

⁸ **Optical Drive.** Due to manufacturing and quality variations in third party optical media (e.g., CD or DVD) or optical media players/recorders, in certain cases, your Toshiba optical drive may not record on certain optical media that bear the applicable logo, or playback optical media recorded by other PCs or optical media recorders. Additionally, certain optical

media recorded on your optical drive may not playback or operate properly on other PCs or optical media players. These problems are not due to any defect in your Toshiba PC or optical drive. Please refer to your PC's product specification for listing of specific format compatibilities.

Recording or viewing of certain optical media may be limited or prevented in accordance with applicable copy protection standards.

⁹ **HD DVD Technology - General.**

Because HD DVD is a new format that makes use of new technologies, certain disc, digital connection and other compatibility and/or performance issues are possible. Advanced interactive and navigation features of the HD DVD Video format including, but not limited to, Picture in Picture (PIP) and network streaming features are not supported by this product. HD DVD Application Logo (HD DVD-ROM) represents the optical drive's conformity with the DVD Forum's verification criteria for HD DVD physical format, and does not represent compliance with the HD DVD Video specification defined by the DVD Forum.

Advanced Access Content System (AACs) keys are integrated into your computer for copy protection purposes. Occasional renewal of the AACs key is required, and easily done by connecting to the Internet. AACs key renewal will be provided at no charge to purchasers. If the AACs key is not renewed, the HD DVD player software will stop playing AACs-protected HD DVD content. However, it will continue to play other forms of content, such as DVD discs or non-protected HD DVD content. For more information on AACs key, visit www.aacsla.com/home.

HD DVD Playback Capabilities.

Depending on HD DVD content, you may experience "frame dropping" or lower performance. HD DVD viewing on external display requires an HDCP capable HDMI™ input. External power required for viewing of HD DVD content. Since CPU power is dedicated to support HD DVD playback function, you must close all other applications during HD DVD playback. Audio content sampled using Linear PCM and having a quality higher than 48kHz/16bit will be down sampled to 48kHz/16bit.

¹⁰ **TV Tuner:** TV tuner will function only in the country where the computer was purchased.

¹¹ **Digital Cable TV Tuner.** To receive digital cable TV channels, including premium programming, you must subscribe to a supported digital cable TV package, install and register your CableCARD and have internet connection. For more information about digital cable services, contact your local cable TV provider. The digital cable TV tuner does not support interactive services including, but not limited to, video-on-demand, pay-per-view or interactive programming guides. The digital cable TV tuner also does not support Satellite TV.

¹² **Display.** Small bright dots may appear on your screen display when you turn on your PC. Your display contains an extremely large number of thin-film transistors (TFT) and is manufactured using high-precision technology. Any small bright dots that may appear on your display are an intrinsic characteristic of the TFT manufacturing technology. Over a period of time, and depending on the usage of the computer, the brightness of the screen will deteriorate. This is also an intrinsic characteristic of the screen technology. When the computer is operated on battery power, the screen will dim and you may not be able to increase the brightness of the screen while on battery power.

¹³ **Graphics (Graphics Processing Unit).**

GPU performance may vary depending on product model, design configuration, applications, power management settings and features utilized. GPU performance is only optimized when operating in AC power mode and may decrease considerably when operating in battery power mode.

Total Available Graphics Memory is the total of, as applicable, Dedicated Video Memory, System Video Memory and Shared System Memory. Shared System Memory will vary depending on system memory size and other factors.

¹⁴ **NVIDIA TurboCache:** When Listing nVIDIA GPU Only – Sample Spec Used Here: [e.g., nVIDIA Quadro® NVS 300M with 128MB or 256MB or 512MB of dedicated graphics memory, nVIDIA Quadro NVS 110M with TurboCache™ with 128MB or 256MB or 512MB of dedicated graphics memory, nVIDIA GeForce™ Go 6200 GPU with TurboCache™ with 32MB or 64MB of dedicated graphics memory or other spec as listed in cookbook]. The revolutionary new nVIDIA GPU utilizes the additional bandwidth of PCI Express to reach higher levels of graphics performance than traditional graphics memory solutions. The nVIDIA GPU shares the capacity and bandwidth of dedicated graphics memory and dynamically available system memory for turbocharged performance and larger total graphics memory. The VRAM capacity indicated in the NVIDIA display is the sum of the discrete graphics memory and the maximum possible graphics memory allocated dynamically by the system memory. The system memory capacity indicated in the Microsoft Windows PROPERTIES display is the maximum possible system memory capacity without adjustment for any system memory which may be dynamically allocated to the graphics system depending on demand.

¹⁵ **Modem Speed.** Due to FCC limitations, speeds of 53 kbps are the maximum permissible transmission rates during download. Actual data transmission speeds will vary depending on line conditions.

¹⁶ **Wireless.** Wireless connectivity and some features may require you to purchase additional software, external hardware or services. Availability of public wireless LAN access points may be limited. The transmission speed over the wireless LAN and the distance over which wireless LAN can reach may vary depending on surrounding electromagnetic environment, obstacles, access point design and configuration, and client design and software/hardware configurations. The actual transmission speed will be lower than the theoretical maximum speed. To use the Atheros SuperAG™ or SuperG™ wireless function, if available, your client and access point must support the corresponding feature. Performance of these functions may vary depending on the format of data transmitted.

¹⁷ **Weight.** Weight may vary depending on product configuration, vendor components, manufacturing variability and options selected.

¹⁸ **Battery Life.** Battery life may vary considerably from specifications depending on product model, configuration, applications, power management settings and features utilized, as well as the natural performance variations produced by the design of individual components. Published battery life numbers are achieved on select models and configurations tested by Toshiba at the time of publication. See "Detailed Specs" for specific battery measurement test. Recharge time varies depending on usage. Battery may not charge while computer is consuming full power. After a period of time, the battery will lose its ability to perform at maximum capacity and will need to be replaced. This is normal for all batteries. To purchase a new battery pack, see the accessories information that shipped with your computer or visit the Toshiba web site at www.accessories.toshiba.com.

Battery life will be less than when using similar applications in the Windows Operating System

¹⁹ **Software.** Some software may differ from its retail version (if available), and may not include user manuals or all program functionality.

Certain Microsoft® software products (including Microsoft Office Small Business Accounting if applicable) included with this computer may use technological measures for copy protection. IN SUCH EVENT, YOU WILL NOT BE ABLE TO USE THE PRODUCT IF YOU DO NOT FULLY COMPLY WITH THE PRODUCT ACTIVATION PROCEDURES. Product activation procedures and Microsoft's privacy policy will be detailed during initial launch of the product, or upon certain reinstallations of the software products or reconfigurations of the computer, and may be completed by Internet or telephone (toll charges may apply).

Internet access is required to enable certain functionality of certain Microsoft products (including Microsoft Office Small Business Accounting 2006) which may be included with this computer.

The Microsoft Office 2007 60-Day Trial software (if applicable) is intended for evaluation purposes only. You must activate the software before you can use it. Product activation procedures will be detailed during initial launch of the software; activation requires Internet access. This software has an expiration date of 60 days from date of first use, at which time the software will operate under reduced-functionality mode, limiting end-user options and operations. The Microsoft Office 2007 60-Day Trial software is distributed without

charge to the End User Customer but if the End User wants to continue to use such product after the trial period, then the End User Customer will have to pay a fee for the perpetual version of such Office Product.

For systems with Microsoft Money Essentials 2007 installed, note that some online services for Microsoft® Money 2007 and Microsoft® Money 2007 Essentials will expire on the earlier of two years after your activation of the software or September 1, 2009. Also, you may need to get some online services separately from your financial institution, which may charge a fee. See the online services policy at <http://money.msn.com/Money/2007/OSP.asp>.

²⁰ **Temperature (Environmental) Conditions.** All temperature references are approximate and the performance of your computer may vary from specifications even when operating within the recommended temperature range.

²¹ **RoHS.** This notebook is compatible with European Union Directive 2002/95/EC, Restriction of the use of certain Hazardous Substances in electrical and electronic equipment (RoHS), which restricts use of lead, cadmium, mercury, hexavalent chromium, PBB, and PBDE. Toshiba requires its notebook component suppliers to meet RoHS requirements and verifies its suppliers' commitment to meeting RoHS requirements by conducting component sampling inspections during the product design approval process.

²² **Warranty:** The terms and conditions of Toshiba's standard limited warranty are available at www.warranty.toshiba.com.

²³ **Service Plans:** The terms and conditions of service upgrade and extension plans offered by Toshiba are available at www.pcsupport.toshiba.com.